



The mounting MM09 kit allows the assembly and disassembly of a shut-off valve. Thanks to the cutting it is possible to study each of the different components and their operation, for example, it is possible to observe how with this type of valves it is sought to avoid a sudden cut of the supply that originates the water hammer. The material is supplied placed and protected in a box for transport along with the necessary tools for its use.

The practice contains the necessary instructions for the assembly and disassembly of both devices, in addition to the necessary guidelines to carry out the maintenance and repair of the same.

CHARACTERISTICS OF WORK AND TESTING OF THE VALVE

- Nominal size of diameter 25 mm.
- Maximum resistance or tightness of maximum cover of 24 kg/cm<sup>2</sup>.
- Maximum tension of seats 18 kg/cm<sup>2</sup>.
- Maximum working pressure 16 kg/cm<sup>2</sup>.